# **INSONO AF3 ADHESIVE**



TECHNICAL DATA SHEET 250203SCANE

(supersedes 200814SCANE)

#### DESCRIPTION

INSONO AF3 ADHESIVE is a homogeneous solvent free, low odour, acrylic latex emulsion based adhesive. INSONO AF3 ADHESIVE is used for interior installation of INSONO AF3 acoustic membrane.

# **RECOMMENDED SUBSTRATES**

- · Properly prepared, clean, dry, fully cured concrete (at least 28 days old), free of moisture, rising moisture and alkaline conditions.
- · Cementitious screeds, mortar beds, gypsum-based concrete and cement-based levelling plasters.
- Exterior Plywood.

# **SURFACE PREPARATION**

Surfaces must be clean and dry, free of oil, grease, dirt, or debris.

# **APPLICATION**

INSONO AF3 ADHESIVE is ready-to-use. No mixing required.

#### 1. ÉTAPES D'APPLICATION

- 1.1. Remove the container lid.
- 1.2. Pour into a pan or spread directly on the substrate.
- 1.3. Apply the adhesive using a 10 mm (3/8 in) nap rollers.
- 1.4. Set the INSONO AF3 membrane while the adhesive is fresh. Do not alow the adhesive to skin over or dry before applying the membrane.

**Application temperature:** between 10 °C (50 °F) and 35 °C (95 °F).

#### FOR COMPLETE INFORMATION ON PRODUCT APPLICATION, PLEASE CONSULT YOUR SOPREMA REPRESENTATIVE.

#### GENERAL INFORMATION

Specifications	INSONO AF3 ADHESIVE
Physical state	Viscous liquid
Base	Acrylic Latex
Colour	Beige
Container	19 L (5.0 US gal)
Weight, per 19 L (5 U.	density 1.19 kg/L (10.0 lb/US gal)   5 gal) container 22.5 kg (50 lb)
Coverage rate, <sup>(1)</sup> per 19 L (5 US gal) container	65 to 84 m² (688 to 904 ft²)
Reaction times,	wet open time approx. 30 minutes curing time (2) 2 to 6 hours

<sup>(1):</sup> Coverage rate is approximate and may vary due to the application technique and surface roughness.



SOPREMA.CA 1877 MAMMOUTH

<sup>(2):</sup> Curing time was determined under ideal application conditions, at 23 °C (73 °F) and 50% relative humidity. Curing time will be longer at lower temperatures.

# **INSONO AF3 ADHESIVE**



TECHNICAL DATA SHEET 250203SCANE

(supersedes 200814SCANE)

#### **PROPERTIES**

Properties	Standards	INSONO AF3 ADHESIVE
Flash point	N/A	Non-flammable
Freeze/thaw stability		Up to 5 °C (41 °F)
Bonding to support		min. 0.31 mPa (45 psi)
Bonding to the INSONO AF3 membrane		min. 0.21 mPa (30 psi)

#### **CLEANING**

- Tools and uncured INSONO AF3 ADHESIVE can be cleaned with water.
- · If the INSONO AF3 ADHESIVE is cured, clean with solvents, such as mineral spirits, Varsol or xylene.

# STORAGE AND HANDLING

The shelf life of INSONO AF3 ADHESIVE is 24 months, when properly kept in the original sealed container. Containers must be stored in a ventilated place, away from heat, frost and direct sunlight.

FOR MORE INFORMATION, REFER TO THE INSTRUCTIONS ON THE CONTAINER LABEL AND RELEVANT SAFETY DATA SHEET (SDS).